



FER102 RETROFIT GANGABLE BOX






FER102C (SOLD SEPERATELY) ADDS 17.5 IN³ VOLUME PER GANG

EXAMPLE:

3-GANG 51.5 IN³ VOL. 4-GANG 69.0 IN³ VOL. 5-GANG 86.5 IN³ VOL. 6-GANG 104.0 IN³ VOL. 7-GANG 121.5 IN³ VOL. 8-GANG 139.0 IN³ VOL.



If you have any questions or if parts are missing Please call our Customer Service Department at 1-800-233-4717. Do not call or return this product to your local store or distributor.

Assembly Instructions:


1. Attach FER1 02 sections together by tilting each piece as shown and by inserting the tabs into the slots in bottom of each piece. Then rotate and snap the sections together along the sides of each piece.

2. If necessary, use same assembly method to attach FER1 02C center sections (sold seperately) to create 3-10 Gang Installations.


FER102

CUT-OUT DIMENSIONS:

2-GANG 3-3/4" HIGH × 3-7/8" WIDE 3-GANG 3-3/4" HIGH × 5-11/16" WIDE 4-GANG 3-3/4" HIGH × 7-1/2" WIDE 5-GANG 3-3/4" HIGH × 9-5/16" WIDE 6-GANG 3-3/4" HIGH × 11-1/8" WIDE 7-GANG 3-3/4" HIGH × 12-15/16" WIDE 8-GANG 3-3/4" HIGH × 14-3/4" WIDE



To disassemble box - insert a flat blade screw driver between ribs as shown and rotate screw driver. Repeat on opposite side.



(FEN102 Nail-On Gangable Box shown - Procedure is the same for the entire series of FEN102 Boxes)

WARNING: When Installing Box, Make sure power is OFF at main panel box before installing. NOTE: All Wiring Must be According to NEC, State and Local Codes.

The manufacturer and distributor warrant this product for material and workmanship only, and shall not be liable for any special incident or consequential damages or for damages or loss caused by improper use or installation.